

 SILICON LABS |  matter

# Matter SoC and Module Selector Guide

Selecting the Right Matter Device for Your Applications





# Table of Contents

## How Silicon Labs' Portfolio is Ideal for Matter Development

- 1 Why Choose Silicon Labs for Matter Development?
- 2 Wireless Hardware for Matter
- 3 Pre-Certified Wireless Software for Matter
- 4 Matter Security Solutions
- 5 Secure Programming
- 6 Most Complete Matter Development Solution

## Matter Selector Guide

- 1 High-Performance, Low-Power Wireless SoCs for Thread and Wi-Fi
- 2 Benefits of Silicon Labs' Thread Solutions
- 3 Benefits of Silicon Labs' Wi-Fi Solutions
- 4 Choosing the Right Products
- 5 Hardware Comparison for Thread: MG24 vs. MG21 vs. MR21
- 6 Hardware Comparison for Wi-Fi: 917 vs. 915 vs. RS9116

## Matter Development Kits

- 1 Solutions for All Matter Use-Cases
- 2 Solutions for Matter Over Thread
- 3 Solutions for Matter Over Thread, Pro Kit Add-Ons
- 4 Solutions for Matter Over Wi-Fi
- 5 About Silicon Labs




# How Silicon Labs' Portfolio is Ideal for Matter Development



## Hardware

### Single-SoC Matter solutions


- **High-performance RF** enables reliable connectivity in every room of the house and beyond
- **Ultra-low-power** — Extend battery life and recharging interval
- **Fully integrated MCU** — Simplify product design, reduce BoM costs, improve profits
- **RF-Certified Modules** — Accelerate time-to-market by up to 9 months



## Software

### Pre-certified and tested Matter, Wi-Fi, Thread, and Bluetooth software


- **Pre-certified** and tested Matter, Wi-Fi, Thread, and Bluetooth software
- **Full compliance** and maximum performance on Silicon Labs hardware
- **Reduce time and costs** of development and certification
- **Improve** product quality
- **The best SDK support** with 10 years of longevity



## Security

### Fully Matter-compliant security


- **Secure Vault** covers all mandatory, recommended, and optional security requirements
- **PSIRT** offers constant monitoring and rectification of vulnerabilities (Matter requirement)
- **MG24** — The highest PSA Level 3 certification
- **SiWx917** — The best-in-class IoT security in Wi-Fi



## Secure Programming

### Securely program Matter certificates, security settings, keys, and flash software


- **Prevent** counterfeiting and IP theft
- **Simplify** the creation of Matter QR codes
- **Reduce** manufacturing risks and costs
- **Accelerate** production time



## Developer Journey

### Most comprehensive end-to-end guide for Matter


- **Reduces your Matter learning curve** to get you to market faster
- **Step by step guide** from learning to production
- **Includes information** on Ecosystems steps along the journey
- **Provides guidance** on hardware including ICs, Modules, and development hardware



## Most Complete

### Most Complete Go-to-Market Solution for Matter

- **Enhance user experience** with high-performance wireless and ultra-low-power
- **Matter-compliant security** to protect devices, users, and brand reputation
- **Develop faster and reduce costs** with community support 24/7, developer journeys, and documentation





# Wireless Hardware for Matter



## Performance

Improve overall product quality, enhance user experience, reduce warranty returns, and minimize support costs through reliable wireless connectivity in every room of the house (and beyond)



## Battery Life

Score better on product reviews and enhance user experience with extended battery life and improved recharging intervals on your devices



## Security

Stay protected with the industry's most advanced IoT security solution, Secure Vault, which is fully compliant with the Matter specification



## Costs & Simplicity


Simplify product designs, reduce BoM costs, and improve your profits using Silicon Labs Matter solutions based on single chip SoCs and modules




# Pre-Certified Wireless Software for Matter

Our SDKs provide pre-certified and tested wireless protocol stacks for Wi-Fi, Thread, Bluetooth LE, and Matter application layer firmware.


Silicon Labs wireless protocol stacks are tested and quality assured for full compliance, stability, and maximum performance to:



Increase overall product quality




Reduce development time and costs




Ensure that devices can pass final certifications on the first go

TESTED & PRE-CERTIFIED SOFTWARE



## Matter Security Solutions



### Fully Compliant

Secure Vault, PSIRT, and CPMS provide the functions needed to cover all mandatory, recommended, and optional security requirements of the Matter specification in one package



### Most Advanced

Featuring advanced IoT security solutions, our MG24 supports the highest PSA Level 3 certification and SiWx917 features the IoT security



### Always Up-to-Date

Continuously monitor vulnerabilities and receive timely security updates. With us, you get the best support service in the industry, with up to 10 years of longevity for software and security



### Programmable

Safely program Matter certificates, keys, security settings, applications, and bootloaders on wireless SoCs to reduce risks, save costs, and accelerate production

## Secure Programming



### Ready to Ship

With CPMS, securely program all Matter certificates, security settings, keys, applications, and bootloaders. Onboarding Payload is provided for the QR code, so Matter products are ready to ship



### Accelerate Production

Instead of separate programming and flashing (in-house/CM), Silicon Labs programs SoCs during production and can deliver Matter-related programming as part of the process; reduces risk, cost, and time-to-market



### Reduce Risks

Wireless SoCs are delivered to the CM secured and programmed with an encrypted SW image, preventing counterfeiting and IP theft



### Maximize Security


Achieve maximum protection with Silicon Labs Secure Vault, which is broadly recognized as the most advanced IoT security solution and is fully compliant with the Matter specification

## Most Complete Matter Development Solution




### Learn in Advance

Access the most comprehensive Matter developer journeys for popular ecosystems like Google, Amazon, Apple, and SmartThings; these journeys help development teams learn the entire process in advance to avoid common mistakes and plan resources wisely



### Kits for all Use-cases

Leverage development kits for all Matter use cases: Matter over Wi-Fi, Matter over Thread, Border Router, Matter Bridge, and more



### Tools for all

No Code to Pro Code, our Simplicity Studio can meet the demands of an RF specialist with no embedded code experience to a team of embedded developers



### Advanced Development


Key features like our Packet Trace Interface for advanced network debug is critical for mesh networks like Matter over Thread, while our Energy Profiler can help deliver the lower power solution, extending battery life of both our Matter over Thread and Matter over Wi-Fi solutions

# High-Performance, Low-Power Wireless SoCs for Thread and Wi-Fi


- Lowest power on the market for Wi-Fi
- Industry-leading wireless characteristics (TX power, RX sensitivity, etc.)
- Single-SoC Matter solutions with Bluetooth LE co-existence
- Integrated wireless MCUs with many add-ons: AI/ML, Sensor Hub, high-accuracy ADC, etc.
- Most advanced security with PSA Level 3 certification for Matter, Thread, Bluetooth LE

One of the first design considerations you'll encounter is what networking technologies best fit your application. Based on this, you then can decide if your project is best suited for a System-on-Chip (SOC) paradigm or a Network Coprocessor (NCP) paradigm and, for the NCP, what kind of serial communication to use for controlling the coprocessor. This design decision is critical because it will determine the requirements and constraints of both the software and the hardware.

For more information on how to approach this decision, you can read our [Software Design Fundamentals User Guide](#).



# Current and Future Application Support





# Silicon Labs Thread Solutions



Reliable, low-latency, and long-range Thread connectivity for SoC and RCP solutions

- +19.5 dBm output power
- Increased RF sensitivity

#### Single-SoC Matter solution

- Integrated Bluetooth LE Co-ex for easy commissioning

#### Matter-compliant security

- Secure Vault™ High supports the Matter hardware and software security requirements with PSA/SESIP Certification Level 3

#### Higher accuracy for industrial sensors

- 20-bit ADC for more granular output values

#### Extend product lifetime

- Large memory facilitating more features, smooth OTA updates, and longer product lifetime

#### Reduce BOM and PCB footprint while simplifying design

#### Faster AI/ML processing with lower energy consumption

- Integrated AI/ML hardware accelerator enables 2-4X faster ML inferencing and up to 6X lower power compared to non-accelerated processors (depends on the algorithm and model)

Memory – Flash 1536 kB, RAM 256 kB



High-performance and reliable Thread RCP solution for Matter gateways

- +20 dBm output power
- High RF sensitivity

#### Multiprotocol

- Bluetooth LE co-ex for easy device commissioning
- Zigbee

#### Improved Wi-Fi blocking performance

- Prevent interference by filtering out Wi-Fi signals

#### Secure Vault™ High

- The most advanced IoT security with PSA/SESIP Level 3

Memory — Flash 1024 kB, RAM 96 kB



High-performance and reliable Thread RCP solution for Matter gateways

- +20 dBm output power
- Increased RF sensitivity

#### Multiprotocol

- Bluetooth LE co-ex for easy device commissioning

#### Improved Wi-Fi blocking performance

- Prevent interference by filtering out Wi-Fi signals

#### Secure Vault™ Mid

- The most advanced IoT security with PSA/SESIP Level 2

Memory — Flash 512 kB, RAM 64 kB



# Silicon Labs Wi-Fi Solutions



Lowest-power Wi-Fi 6 SoC battery-powered devices

Minimal battery replacement and recharging hassle for users

- Always-on cloud connectivity with minimal power
- Doubling the Wi-Fi 6 battery life compared to the nearest competing SoCs

Improved user experience with superior wireless performance and easy device commissioning

- Bluetooth LE co-existence for commissioning

Devices, users, and brand are protected from cyber threats

- Best-in-Class Security for Wi-Fi

Fully integrated wireless MCU

- Dual core with an application-dedicated ARM core
- High memory, PSRAM
- AI/ML, ultra-low-power sensor hub

Maximum Wi-Fi gateway compatibility

- Independently tested
- Reduce user frustration, customer care costs, and improve brand loyalty
- Comprehensive networking stack (TCP/IP, HTTP/HTTPS, MQTT, etc.)

Seamless integration with Silicon Labs development solutions

- Simplicity Studio 5 streamlines the development process, reducing costs and time-to-revenue



Energy-efficient Wi-Fi 6 SoC for line-powered devices

Improve user experience with exceptional wireless performance and easy device commissioning

- Always-on cloud connectivity
- Wi-Fi 6 for improved connectivity in high-density environments
- Better coverage for devices in every room of the house and beyond (2.4 GHz)
- Bluetooth LE co-ex for easy commissioning

Protect devices, users, brand, and revenue from cyber-threats

- Best-in-class security for Wi-Fi

Maximum Wi-Fi gateway compatibility, independently tested

- Reduce user frustration, customer care costs, and improve brand loyalty

Seamless integration with Silicon Labs development solutions

- Simplicity Studio 5 streamlines the development process, reducing cost and time-to-revenue



Ultra-low-power for Wi-Fi 4 on battery devices

- 55  $\mu$ A stand-by associated current at 1 sec

NCP Matter solutions only

Integrated Bluetooth LE Co-ex for easy commissioning

High-performance Wi-Fi connectivity

- +20 dBm TX, -98 dBm RX, 72 Mbps bandwidth with less power than competitors

Maximum Wi-Fi access point compatibility

- Independently tested across 100s of Wi-Fi access points for exceptional interoperability

Enterprise-level security

- TLS 1.0, TTLS, PEAP, WPA2/WPA3

Pre-certified stack by Wi-Fi Alliance







- Making your end-product certification easier (Est. Q1 2023)

Comprehensive networking stack

- Offloads the main MCU with TCP/IP (IP v4), SSL 3.0/TLS 1.2, HTTP/HTTPS, Web sockets, DHCP, MQTT Client









# Matter 1.0/1.1 Device Types

 <b>Controllers / Bridges</b>	 <b>Lighting, Switches, Plugs</b>	 <b>TVs</b>	 <b>Sensors</b>	 <b>Locks, Shades</b>	 <b>HVAC Controls</b>
<p><b>MG24</b> High-perf Thread RCP, Bluetooth LE co-ex Low power, long battery life Long-range, +19.5 dBm TX AI/ML High PSA L3 security</p> <p><b>MG21</b> Thread RCP for gateways Bluetooth LE co-ex &amp; Multiprotocol Long range, +20 dBm TX Low power, long battery life High PSA L3 security</p> <p><b>MR21</b> Thread RCP for gateways Bluetooth LE co-ex Low power, long battery life Long range, 20 dBm TX Secure Vault Mid</p>	<p><b>SiWx917</b> Single-SoC Matter solution Lowest-power Wi-Fi 6 for battery devices Bluetooth LE co-ex Best Wi-Fi IoT security AI/ML CA Title 20</p> <p><b>SiWx915</b> Wi-Fi 6 for line devices Single-SoC Matter solution Bluetooth LE co-ex Best Wi-Fi IoT security CA Title 20</p>	<p><b>MG24</b> High-perf Thread RCP, Bluetooth LE co-ex Long-range, +19.5 dBm TX AI/ML High PSA L3 security</p> <p><b>MG21</b> Thread RCP for gateways Bluetooth LE co-ex &amp; Multiprotocol Long range, +20 dBm TX High PSA L3 security</p> <p><b>MR21</b> Thread RCP for gateways Bluetooth LE co-ex Long range, +20 dBm TX Secure Vault Mid</p>	<p><b>SiWx917</b> Single-SoC Matter solution Lowest-power Wi-Fi 6 for battery devices Bluetooth LE co-ex AI/ML Best Wi-Fi IoT security ULP Sensor Hub 16-bit ADC</p> <p><b>MG24</b> Thread SoC for battery devices Low power, long battery life Long-range, +19.5 dBm TX Bluetooth LE co-ex AI/ML High PSA L3 security High-accuracy ADC</p>	<p><b>SiWx917</b> Lowest-power Wi-Fi 6 for battery devices Single-SoC Matter solution Bluetooth LE co-ex AI/ML Best Wi-Fi IoT security</p> <p><b>SiWx915</b> Single-SoC Matter solution Wi-Fi 6 for line devices Bluetooth LE co-ex Best Wi-Fi IoT security</p> <p><b>RS9116</b> Lowest power Wi-Fi 4 &amp; Bluetooth LE co-ex for battery devices Matter NCP solution Comprehensive networking stack</p> <p><b>WF200</b> Low-power Wi-Fi 4 only for battery &amp; line devices Matter RCP solution MCU offload Small 4 × 4 mm</p> <p><b>MG24</b> Thread SoC for battery devices Low power, Long battery life Long-range, +19.5 dBm TX Bluetooth LE co-ex AI/ML High PSA L3 security</p>	<p><b>SiWx917</b> Single-SoC Matter solution Lowest-power Wi-Fi 6 for battery devices AI/ML Best Wi-Fi IoT security ULP Sensor Hub</p> <p><b>SiWx915</b> Single-SoC Matter solution Wi-Fi 6 for line devices Bluetooth LE co-ex Best Wi-Fi IoT security</p> <p><b>RS9116</b> Lowest power Wi-Fi 4 &amp; Bluetooth LE co-ex for battery devices Matter NCP solution Comprehensive networking stack</p> <p><b>WF200</b> Low-power Wi-Fi 4 only for battery &amp; line devices Matter RCP solution MCU offload Small 4 × 4 mm</p> <p><b>MG24</b> Single-SoC Matter/Thread solution Low power, long battery life Long-range, +19.5 dBm TX Bluetooth LE co-ex AI/ML High PSA L3 security High-accuracy ADC</p>



# Matter 1.2

# Future Device Types

 <b>White Goods</b>	 <b>Robot Vacuums</b>	 <b>Sensing Controls, Detectors</b>	 <b>Energy Management</b>	 <b>Cameras</b>	 <b>Access Points</b>
<p><b>SiWx917</b>                      Lowest-power Wi-Fi 6 for battery devices                      86 Mbps                      Single-SoC Matter solution                      Bluetooth LE co-ex                      AI/ML                      Best Wi-Fi IoT security                      ULP Sensor Hub q</p>	<p><b>SiWx917</b>                      Lowest-power Wi-Fi 6 for battery devices                      Single-SoC Matter solution                      Bluetooth LE co-ex                      AI/ML                      Best Wi-Fi IoT security</p>	<p><b>SiWx917</b>                      Lowest-power Wi-Fi 6 for battery devices                      Single-SoC Matter solution                      Bluetooth LE co-ex                      AI/ML                      Best Wi-Fi IoT security                      ULP Sensor Hub                      16-bit ADC</p>	<p><b>SiWx917</b>                      Lowest-power Wi-Fi 6 for battery devices                      86 Mbps                      Single-SoC Matter solution                      Bluetooth LE co-ex                      AI/ML                      Best Wi-Fi IoT security                      ULP Sensor Hub</p>	<p><b>SiWx917</b>                      Lowest-power Wi-Fi 6 for battery devices                      86 Mbps                      Single-SoC Matter solution                      Bluetooth LE co-ex                      AI/ML                      Best Wi-Fi IoT security                      ULP Sensor Hub</p>	<p><b>MG24</b>                      High-perf Thread RCP, Bluetooth LE co-ex                      Low power, long battery life                      Long-range, +19.5 dBm TX                      AI/ML                      High PSA L3 security</p>
<p><b>SiWx915</b>                      Wi-Fi 6 for line devices                      86 Mbps                      Single-SoC Matter solution                      Bluetooth LE co-ex                      Best Wi-Fi IoT security</p>		<p><b>MG24</b>                      Thread SoC for battery devices                      Low power, long battery life                      Long-range, +19.5 dBm TX                      Bluetooth LE co-ex                      AI/ML                      High PSA L3 security                      High-accuracy ADC</p>	<p><b>SiWx915</b>                      Wi-Fi 6 for line devices                      86 Mbps                      Single-SoC Matter solution                      Bluetooth LE co-ex                      Best Wi-Fi IoT security</p>	<p><b>SiWx915</b>                      Wi-Fi 6 for line devices                      86 Mbps                      Single-SoC Matter solution                      Bluetooth LE co-ex                      Best Wi-Fi IoT security</p>	<p><b>MG21</b>                      Thread RCP for gateways                      Bluetooth LE co-ex and Multiprotocol                      Long range, +20 dBm TX                      Low power, long battery life                      Secure Vault High</p>
<p><b>RS9116</b>                      Lowest power Wi-Fi 4 and Bluetooth LE co-ex for battery devices                      Matter NCP solution                      Comprehensive networking stack                      72 Mbps</p>	<p><b>RS9116</b>                      Thread SoC for battery devices                      Low power, long battery life                      Long-range, +20 dBm TX                      Bluetooth LE co-ex                      AI/ML                      High PSA L3 security</p>		<p><b>RS9116</b>                      Lowest power Wi-Fi 4 &amp; Bluetooth LE co-ex for battery devices                      Matter NCP solution                      Comprehensive networking stack                      72 Mbps</p>	<p><b>RS9116</b>                      Lowest power Wi-Fi 4 &amp; Bluetooth LE co-ex for battery devices                      Matter NCP solution                      Comprehensive networking stack                      72 Mbps</p>	<p><b>MR21</b>                      Thread RCP for gateways                      Bluetooth LE co-ex                      Low power, long battery life                      Long range, 20 dBm TX                      Secure Vault Mid</p>
<p><b>WF200</b>                      Low-power Wi-Fi 4 only for battery and line devices                      Matter RCP solution                      MCU offload                      72 Mbps                      Small 4 × 4 mm</p>			<p><b>WF200</b>                      Low-power Wi-Fi 4 only for battery and line devices                      Matter RCP solution                      MCU offload                      72 Mbps                      Small 4 × 4 mm</p>	<p><b>WF200</b>                      Low-power Wi-Fi 4 only for battery and line devices                      Matter RCP solution                      MCU offload                      72 Mbps                      Small 4 × 4 mm</p>	



# MG24 vs. MG21 vs. MR21



	MG24	MG21	MR21
<b>Protocol Support</b>	RCP SoC - Dynamic Multiprotocol w/ Bluetooth LE Supports OTA with internal flash	Multiprotocol, Proprietary Bluetooth, Thread, and Zigbee (NCP and SoC) Matter (RCP only)	Bluetooth (HCI) OpenThread (RCP multi-PAN) Zigbee1 (RCP - requires separate license for Zigbee stack) Matter over Thread (RCP multi-PAN + BT HCI)
<b>Frequency Bands</b>	2.4 GHz	2.4 GHz	2.4 GHz
<b>Core</b>	Cortex-M33 (78 MHz)	Cortex-M33 (80 MHz)	Cortex-M33 (80 MHz)
<b>Max Flash</b>	1536 kB	1024 kB	512 kB
<b>Max RAM</b>	256 kB	96 kB	64 kB
<b>Security</b>	Secure Vault Mid Secure Vault High	Secure Vault Mid Secure Vault High	Secure Vault Mid
<b>Rx Sensitivity (15.4)</b>	-105.4 dBm	-104.5 dBm	-104.3 dBm
<b>Rx Sensitivity (Bluetooth LE 1Mbps)</b>	-97.6 dBm	-97.5 dBm	-97.1 dBm
<b>Active Current</b>	33.4 $\mu$ A/MHz	59.8 $\mu$ A/MHz	59.7 $\mu$ A/MHz
<b>Sleep Current (EM2, 16 kB ret)</b>	1.3 $\mu$ A	4.5 $\mu$ A	25 $\mu$ A
<b>TX Current @ +0 dBm (2.4 GHz)</b>	5.0 mA	9.3 mA	9.3 mA
<b>TX Current @ +10 dBm (2.4 GHz)</b>	19.1 mA	34 mA	60.8 mA (+20 dBm OPN)
<b>TX Current @ +20 dBm (2.4 GHz)</b>	156.8 mA	185 mA	186.5 mA
<b>RX Current (802.15.4)</b>	5.1 mA	9.5 mA	9.5 mA
<b>RX Current (Bluetooth LE 1 Mbps)</b>	4.4 mA	8.8 mA	8.8 mA
<b>Serial Peripherals</b>	USART, EUSART, I2C	USART, I2C	USART
<b>Analog Peripherals</b>	20-bit ADC, ACMP, VDAC	12-bit ADC, ACMP	
<b>Other</b>	Die Temp Sensor	Die Temp Sensor	Die Temp Sensor
<b>Operating Voltage</b>	1.71 to 3.8 V	1.71 to 3.8 V	1.71 to 3.8 V
<b>GPIO</b>	26, 28/32	20	20
<b>Package</b>	5x5 QFN40, 6x6 QFN48 12.9x15.0 PCB Module	4x4 QFN32	4x4 QFN32



# 917 vs. 915 vs. RS9116



Parameter	SiWx917	SiWx915	RS9116
<b>Sampling / In-Production</b>	Sampling now, Q4 2023	Sampling/IP: Q1, 2024	In production
<b>RF Bands (GHz)</b>	2.4 GHz	2.4 GHz	2.4 GHz, 5 GHz (Modules)
<b>Wi-Fi Generation / Bandwidth</b>	Wi-Fi 6 / 20 MHz (OFDMA, MU-MIMO, TWT)	Wi-Fi 6 / 20 MHz (OFDMA, MU-MIMO, TWT)	Wi-Fi 4 / 20 MHz
<b>Bluetooth Support</b>	Bluetooth LE 5.1	Bluetooth LE 5.1	BT (SPP, A2DP), Bluetooth LE 5
<b>Modes of Operation</b>	RCP, NCP, SoC	RCP, NCP, SoC	RCP, NCP
<b>Temperature Range</b>	-40 to 105° C	-40 to 85° C	-40 to 85° C
<b>PSRAM, AI/ML</b>	Yes	No	No
<b>Embedded SRAM and FLASH</b>	672 kB and up to 8 MB; opt ext. flash	672 kB and up to 4 MB; opt ext. flash	384 kB and 4 MB
<b>NWP Type / Speed (MHz)</b>	TA-4T / 160 MHz	TA-4T / 160 MHz	TA-4T / 160 MHz
<b>MCU Type / Speed (MHz)</b>	Cortex M4F / 180 MHz	Cortex M4F / 180 MHz	N/A
<b>Security</b>	WPA2/WPA3, SSL/TLS 1.3 PSA-L2 TRNG, PUF, Secure Boot, Secure OTA, Secure Zone, Secure XIP (AES-XTS), Advanced Crypto	WPA2/WPA3, SSL/TLS 1.3 PSA-L2 TRNG, PUF, Secure Boot, Secure OTA, Secure Zone (TEE), Secure XIP (AES-XTS), Advanced Crypto	WPA2/WPA3, SSL/TLS 1.2
<b>Max GPIO (GPIO Multiplexer)</b>	46	22	N/A
<b>IC Pkg</b>	7x7 QFN84, PCB Module	6x6 QFN52, PCB Module	7x7 QFN84, SiP and PCB Modules
<b>WLAN Max Tx Power / Rx Sens</b>	21 dBm / -98 dBm	21 dBm / -98 dBm	20 dBm / -98 dBm
<b>Power Modes</b>	Ultra-Low-Power	Low-Power	Ultra-Low-Power
<b>Target Applications</b>	Door Locks, HVAC, Portable Medical, Sensors, Cameras, Switches, Power Tools, Asset Monitoring, Fleet Management, Clinical Medical, Metering	Appliances, HVAC, Portable Medical, Cameras, Switches, Power Tools, Asset Monitoring, Fleet Management, Clinical Medical, Metering	Speakers, Door Locks, HVAC, Portable Medical, Wear- ables, Power Tools, Asset Monitoring, Fleet Management, Clinical Medical



# Solutions for All Matter Use-Cases


Development solutions for all Matter use-cases:

- Matter over Wi-Fi
- Matter over Thread
- OpenThread Border Routers
- Matter Bridge for Zigbee and Z-Wave

AVAILABLE NOW  
Matter Development Solutions


## Matter Border Router / Bridge

Matter | Thread | Bluetooth




## Matter over Wi-Fi 4 (End Node)

Matter | Wi-Fi | Bluetooth




## Matter over Wi-Fi 6 (End Node)

Matter | Wi-Fi | Bluetooth



## Matter over Thread (End Node)

Matter | Thread | Bluetooth






# Solutions for Matter Over Thread



## Pro Kit

EFR32xG24

Pro Kit with the MG24 SoC and BRD4187C Radio Board is THE development tool for Matter innovators! All tools for developing wireless applications. Enhance with Add-on radio boards!



[Learn More](#)

## Dev Kit

EFR32xG24

A small, cost-effective, and feature-rich development kit based on the MG24 SoC for prototyping and experimenting with energy-friendly Matter devices; supports Qwik and Ada Fruit boards




[Learn More](#)

## Explorer Kit

EFR32xG24

An ultra-low-cost board for rapid Matter prototyping and concept creation on the MG24 SoC



[Learn More](#)

# Solutions for Matter Over Thread


Pro Kit Add-Ons



## Radio Board

+10 dBm EFR32xG24 Wireless 2.4 GHz

Works with the MG24 Pro Kit; supports Bluetooth LE, Thread, Matter, and other protocols




[Learn More](#)

## Antenna Diversity

+20 dBm EFR32xG24 Wireless 2.4 GHz

Established for antenna diversity development; designed for managing multipath fading on the MG24 Pro Kit (includes reference)




[Learn More](#)

## Radio Board

+20 dBm EFR32xG24 Wireless 2.4 GHz

Works with the MG24 Pro Kit to support Bluetooth LE, Thread, Matter, and other protocols



[Learn More](#)




# Solutions for Matter Over Wi-Fi




## SiWx917 Dev Kit for SoC Mode

Radio board with SiWx917 that plugs into the Pro Kit baseboard; radio board provides access to the SiWx917 MCU peripherals and the internal application MCU for development using Simplicity Studio IDE and Debugger



## SiWx917 Dev Kit for NCP/RCP Modes

For RCP and NCP hosted modes of operation, the expansion board plugs into an existing EFR32MG24 Pro Kit to enable the development of hosted applications, including Matter on the MG24




# Solutions for Matter Over Wi-Fi



## RS9116X EVK2 Wi-Fi + Bluetooth Dev Kit


Works with the MG24 Pro Kit;  
supports Bluetooth LE, Thread, Matter,  
and other protocols



[Learn More](#)

## RS9116X EVK1 Wi-Fi + Bluetooth Dev Kit


Established for antenna diversity development;  
designed for managing multipath fading on the  
MG24 Pro Kit (includes reference)



[Learn More](#)

## RS9116X Dual Band Wi-Fi + Bluetooth Development Kit (CC1 Module)

Supports Dual Band Wi-Fi 4 802.11 a/b/g/n  
on the 2.4 & 5 GHz bands and dual-mode  
Bluetooth, allowing designers to develop  
applications for the RS9116 CCx modules



[Learn More](#)



# Solutions for Matter Over Wi-Fi



## SLEXP8022C - WF200 Wi-Fi Expansion Kit with Raspberry Pi


Allows development on the WF200 Series of Wi-Fi Transceiver SoCs; includes a built-in Raspberry Pi Connector to get started immediately with Linux development and an EXP Connector to enable development on Silicon Labs' MCUs and Wireless MCUs



[Learn More](#)

## SLEXP8023C - WFM200S Wi-Fi Expansion Kit with Raspberry Pi

Enables development for the WFM200S Wi-Fi Transceiver modules



[Learn More](#)

# About Silicon Labs

Silicon Labs is the leading provider of silicon, software, and solutions for a smarter, more connected world. Our industry-leading wireless solutions feature a high level of functional integration. Multiple complex mixed-signal functions are integrated into a single IC or system-on-chip (SoC) device, saving valued space, minimizing overall power consumption requirements, and improving products' reliability. We are the trusted partner for the world-leading consumer and industrial brands. Our customers develop solutions for a wide range of applications, from medical devices to smart lighting to building automation, and much more.

